


TECHNICAL DATA SHEET – PRONTO™

PRODUCT: PRONTO™ Kombi Spot Putty
TECHNICAL CALLS: 1-800-321-0672



DESCRIPTION:

PRONTO™ Kombi Spot Putty is a single component, ultra smooth and fast drying putty that is ideal for use on small, last minute repairs. This ready to use putty is formulated for excellent adhesion to properly prepared metal, galvanized, aluminum, primers and existing finishes.

PART NUMBERS:

- 32046 PRONTO™ 5 oz. tube 12 tubes / case 5 lbs / case

PRODUCT USES:

Ideal for last minute repairs, minor imperfections, pinholes, surface flaws and scratch marks in body repair work.

TYPICAL SUBSTRATES:

- Metal • Aluminum • Galvanized and other zinc-coated steel • 1K and 2K Primers
- Aged, sanded OEM topcoats



SURFACE PREPARATION:

Clean surface of all contaminants with wax & grease remover such as 1240-1. Sand surface. Clean with wax & grease remover. Dry thoroughly.

APPLICATION:

1 – 3 thin coats, allowing 15 minutes in between coats (@ 72° F / 22° C). **Note:** Avoid excessive film build.

FINISHING: **Dry Time:** 20 minutes (@ 72° F / 22° C) 10 minutes (@ 100°F / 40°C)

TOPCOATING: May be topcoated with primer, primer surfacer, sealer, basecoat and single stage refinish coatings.



TECHNICAL INFORMATION:

Appearance: Olive Drab
Mix Ratio: RTU
V.O.C.: 3.31 lbs. /gal 396 g/l
Pot Life : Tack free time 45 – 90 seconds (depending upon thickness & temperature)
Solids: 75.3%

ASSOCIATED MSDS: Putty: “Pronto Putty-32040”



HEALTH & SAFETY:

Read all warnings, first aid and safety for all components before using. Keep out of reach of children and animals. Wear a properly fitting NIOSH/MSHA approved respirator. Select positive pressure supplied respirator (TC-19C or equivalent) for isocyanates. Follow the respirator manufacturer’s directions for use. Protect hands with impervious rubber gloves. Wear face, skin and eye protection. USC products are for industrial use by professional, trained painters.

Emergency Medical or Spill Control Information:

In U.S. or Canada call CHEMTREC at 1-800-424-9300